

Jadoo™ Bare Metal Coronary Stent System



Description:

Features

Optimal Balance of radial strength and flexibility

1. Proprietary DOUBLE-HELIX stent design offers outstanding flexibility and conformability.
2. Optimal thickness of stent strut provides favorable balance between radial strength and deliverability.
3. 3-3-3 corrugated open-cell design offers uniform scaffolding and great flexibility.

Technical Parameters:

Design	Sine wave, 8 crests 3-3-3 link, double-helix design
Material	316L stainless steel, laser cut
Strut Thickness	0.0045"
Technical Parameters	Metal-artery ratio : 15%—18% Crossing profile : 0.9—1.2mm Balloon tip profile : 0.52mm
Nominal Inflation Pressure	8atm
RBP	16atm for 2.5-3.5mm; 14atm for 4.0mm

Ordering Information

Stent diameter(mm)	Stent Length and Catalogue Number							
	9mm	12mm	14mm	16mm	18mm	20mm	22mm	24mm
2.5	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX
	2509	2512	2514	2516	2518	2520	2522	2524
3.0	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX
	3009	3012	3014	3016	3018	3020	3022	3024
3.5	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX
	3509	3512	3514	3516	3518	3520	3522	3524
4.0	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX	LPCSRX
	4009	4012	4014	4016	4018	4020	4022	4024

Contact Info -

www.jadooglobal.com

APAC

A-7, 2nd Floor,
Sector-12,
Noida - 201301
Uttar Pradesh.
INDIA.

M: +91 9718100847
T: +91 -120- 4320242
E: sales@jadooglobal.com

Americas

7231 Spring Ct
West Hills, CA 91307
U.S.A.

T: +1-310-629-9431
E: sales@jadooglobal.com

Australia

Canberra,
Australia.

T: +61 424466808
E: sales@jadooglobal.com